



DEVItronic™

The DEVItronic™ condense heater provides the perfect solution to avoid condensation problems in shielded electrical installations like boards and control cabinets.

DEVItronic™ solves the problem with moisture and condense by increasing the temperature a few degrees above the surrounding temperature.

DEVItronic™ has a large surface and a low surface temperature, and thus the heating element will not damage print and plastic cabinets.

Benefits:

- Rugged construction
- Corrosion-resistant
- IP Class 55

Type	Value
Temperature range	-40 °C to 45 °C
Cold lead	0.5 m
IP Class	IP 55

Types

Item no.	Type	Operation voltage	Effect @ 10°C	H x W x D (mm)	EAN no.
60800075	DEVItronic™ 75 mm	12 - 48 V	15W	75 x 72 x 57	5703435010532
60802071	DEVItronic™ 100 mm	12 - 48 V	20W	100 x 116 x 33	5703435010563
60802204	DEVItronic™ 250 mm	12 - 48 V	40W	100 x 116 x 33	5703435010594
60800109	DEVItronic™ 75 mm	110 - 240 V	15W	75 x 72 x 57	5703435010549
60802105	DEVItronic™ 100 mm	110 - 240 V	20W	100 x 116 x 33	5703435010570
60802253	DEVItronic™ 250 mm	110 - 240 V	40W	250 x 116 x 33	5703435010600
60802113	DEVItronic™ 100 mm	220 - 440 V	20W	100 x 116 x 33	5703435010587
60802261	DEVItronic™ 250 mm	220 - 440 V	40W	250 x 116 x 33	5703435010617
60801156	DEVItronic™ with 50 dg termo, 145 mm	240 V	70W	142 x 72 x 57	5703435010556
60802402	DEVItronic™ with 50 dg termo, 250 mm	240 V	100W	250 x 116 x 33	5703435010624
60802451	DEVItronic™ with 50 dg termo, 250 mm	240 V	160W	250 x 116 x 33	5703435011034